

Rittal – The System.

Faster – better – everywhere.



CP 6148.000

Twin castors

State: 2026-02-01 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6148.000 - Twin castors

For mobile use, can be mounted directly on the enclosure.

Features

Model No.	CP 6148.000
Product description	For mobile use, can be mounted directly on the enclosure.
Color	Black with gray running surface
Supply includes	4 twin castors, 2 x with, 2 x without locks. Assembly components
Suitable for	Enclosure type: VX Enclosure type: VX IT Enclosure type: TS Enclosure type: TS IT Enclosure type: VX SE Enclosure type: PC Enclosure type: TP pedestals Enclosure type: IW Enclosure type: Data Rack Enclosure type: Chiller
Clearance floor	85 mm
Max. load capacity (static) per component	750 N
Suitable for Model No.	6106.200 6106.300
Dimensions	Thread: M12 x 20
Packaging unit	1 pc(s).
Net weight	1.115
Gross weight	1.293
Customs tariff number	39269097
EAN	4028177206007
E-Number Sweden	E7239728

Features

ETIM 9 EC002621

ECLASS 8.0 27189262