### Rittal – The System.

Faster – better – everywhere.





## CP 6315.200

# Operating housing with handle strips

State: 2025-10-16 (Source: rittal.com/ca-en)



#### CP 6315.200 - Operating housing with handle strips

Command panel with handle strips in contemporary design of sheet steel, with  $\emptyset$  130 mm support arm cut-out to fit CP 60/120/180 support arm system, service access optionally from the front or rear, aluminum front panel easily removable for machining, protection category IP 55



#### **Features**

Model No.	CP 6315.200
Material	Housing and door: Carbon steel
	Handle strips: Aluminum
	Front panel: Aluminum
	Cover caps: Plastic
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside,
	textured paint
	Handle strip: Natural anodized
	Front panel: Natural anodized.
Color	Housing and door: RAL 7035
	Handle strip: Natural anodized
	Front panel: Natural anodized.
	Cover caps: Similar to RAL 7024
Supply includes	Housing with cut-out and reinforcement for support arm connection
	Ø 130 mm
	Front with maximum cut-out, covered with easily machinable 3 mm
	aluminum front panel
	Side handle strips and cover caps
	Cam lock with 3 mm double-bit insert
	Integral interior mounting bracket with TS system punchings

© Rittal 2025 2

#### Features

Dimensions	Width: 380 mm
	Height: 300 mm
	Depth: 210 mm
Protection category IP to IEC 60 529	IP 55
Version	Service access from front
Note	The support arm connection and door catch may be swapped over by rotating the enclosure
	Optional: Support arm connection Ø 130 mm, preformed off-center in the reinforcement plate, easily drilled out
	Lock systems for servicing access from the front: 41 mm lock
	inserts, type C, lock cylinder, plastic handles and T-handles, type C
Base material	Aluminum
Note on Model No.:	Compatible mounting plate 5050.430 with shipping bag 5050.507
Lock	Lock version: Sickle-shaped locking nose
	No. of locks: 1
	Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	7.955
Gross weight	8.374
Customs tariff number	94032080
EAN	4028177693944
ECLASS 8.0	27180505

## Approvals

Explanations	Declaration of conformity
·	Declaration of conformity UK

© Rittal 2025 3