


Rittal – The System.

Faster – better – everywhere.



DK 7113.000

Ground rail, horizontal

State: 2025-08-15 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7113.000 - Ground rail, horizontal undefined

Equipotential bonding strips, current carrying capacity approx. 200 A.

Features

| | |
|------------------------------|--|
| Model No. | DK 7113.000 |
| Supply includes | Ground rail made from E-Cu 57 to DIN EN 12 163, DIN EN 13 601, 15 x 5 mm 20 connection points with M5 screws 2 ground connections 25 mm ² 2 isolators Assembly components |
| Dimensions | Width: 15 mm Height: 5 mm Length: 450 mm |
| Suitable for | Enclosure type: AX VX VX IT TS TS IT AX wall-mounted housing, 3-part Width: > 600 mm Depth: > 600 mm Suitable for width/depth: 800 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 0.402 |
| Gross weight | 0.436 |
| Copper weight (kg per piece) | 0.28 |
| Customs tariff number | 74198090 |
| EAN | 4028177124943 |
| E-Number Sweden | E7239683 |
| ETIM 9 | EC000329 |
| ECLASS 8.0 | 27400605 |

Approvals

Explanations

Manufacturer's declaration