

Rittal – The System.

Faster – better – everywhere.



CP 6372.563 Comfort Panel

State: 2025-08-29 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6372.563 - Comfort Panel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability. Protection category IP 65 to IEC 60 529.



Features

Model No.	CP 6372.563
Version	Support arm connection Ø 130 mm
Benefits	Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability Compatible with all Rittal stand and support arm systems
Material	Housing: Extruded aluminum section Corner pieces: Die-cast zinc Corner protectors: Plastic
General color	Natural anodized
Color	Housing: Natural anodized. Corner pieces: RAL 7035 Corner protectors: Similar to RAL 7024
Supply includes	Enclosure with cut-out for support arm connection 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C Seals and assembly components for front panels Rear panel screwed, enclosure hinged at the front with side double-bit lock insert

Features

Dimensions	Width: 628.5 mm Height: 708.5 mm Depth: 209 mm
Installation depth	191 mm
Protection category IP to IEC 60529	IP 65
Protection category NEMA	NEMA 12
Suitable for front panel width	520 mm
Suitable for front panel height	600 mm
Version	Service access from rear
Note	The support arm connection may be swapped over by rotating the enclosure
Base material	Aluminum
Lock	Lock version: Sickle-shaped locking nose No. of locks: 2 Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	18.7
Gross weight	20.34
EAN	4028177663145
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK