

Rittal – The System.

Faster – better – everywhere.



DK 7241.005

Fiber-optic splicing box, depth-variable

State: 2026-07-08 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7241.005 - Fiber-optic splicing box, depth-variable

To accommodate splicing cassettes.



Features

Model No.	DK 7241.005
Product description	The 482.6 mm (19") splicing box is used to hold splicing cassettes and can be installed in any network distributor within the 482.6 mm (19") rail and can be used as a fiberoptic end closure or distributor. The variable cassette accommodates the twist-proof installation of all standard splicing cassettes. The rear part of the splicing box is left completely open for cable routing, with a rubber clamping profile that provides protection from the ingress of dust. The fiberoptic cables can be secured using cable ties or cable clamps. The splicing box is infinitely depth-adjustable within the 482.6 mm (19") flange up to 100 mm. In addition, the splicing box can be completely removed from the 482.6 mm (19") flanges. Two strain relief clamps and the cable routing clips for the fiber dispenser provide a system-compatible solution for all fiberoptic cabling.
Material	Carbon steel
Color	RAL 7035
Supply includes	Splicing box Cable routing clips Box type plug-in unit cover Mounting accessories for patch panel
Number of splicing cassettes max	2
Note	Supplied without patch panels and splicing cassettes
Installation depth	302 mm

Features

Height units	1 U
Packaging unit	1 pc(s).
Net weight	3.155 kg
Gross weight	3.355 kg
PCF/VE (cradle-to-gate)	12.8 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
ETIM 9	EC001130
ECLASS 8.0	19170113
Product description	DK Fibre-optic splicing box, 1 U, For D: 302 mm, without pull-out, depth-variable