Rittal – The System.

Faster - better - everywhere.





CP 6380.000 Optipanel

State: 2025-10-27 (Source: rittal.com/ca-en)



CP 6380.000 - Optipanel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Extremely slim design, requires slightly more space than the installations themselves.







Features

CP 6380.000
Support arm connection, rectangular 120 x 65 mm
Aluminum housing, high thermal conductivity for optimum passive
heat dissipation.
Low weight coupled with high stability
Compatible with all Rittal stand and support arm systems
Housing: Extruded aluminum section
Corner pieces: Die-cast zinc
Corner protectors: Plastic
Natural anodized
Housing: Natural anodized.
Corner pieces: RAL 7035
Corner protectors: Similar to RAL 7024
Housing with hinged rear panel
Seals
Width: 526.6 mm
Height: 354.3 mm
Depth: 110 mm

© Rittal 2025 2

Features

Installation depth	100 mm
Protection category IP to IEC 60 529	IP 65
Suitable for front panel width	482.6 mm
Suitable for front panel height	310.3 mm
Version	Service access from rear
Note	The support arm connection may be swapped over by rotating the enclosure 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C Rear panel hinges on the longest enclosure side
Base material	Aluminum
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	5.86
Gross weight	6.168
Customs tariff number	94032080
EAN	4028177231627
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3