

Rittal – The System.

Faster – better – everywhere.



CP 6380.610

Optipanel

State: 2026-01-31 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6380.610 - Optipanel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Extremely slim design, requires slightly more space than the installations themselves.



Features

Model No.	CP 6380.610
Version	Support arm connection Ø 130 mm
Benefits	Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability Compatible with all Rittal stand and support arm systems
Material	Housing: Extruded aluminum section Corner pieces: Die-cast zinc Corner protectors: Plastic
General color	Natural anodized
Color	Housing: Natural anodized. Corner pieces: RAL 7035 Corner protectors: Similar to RAL 7024
Supply includes	Housing with hinged rear panel Seals Seals and assembly components for front panels
Installation depth	150 mm

Features

Protection category IP to IEC 60529	IP 65
Suitable for front panel width	520 mm
Suitable for front panel height	600 mm
Version	Service access from rear
Note	<p>The support arm connection may be swapped over by rotating the enclosure</p> <p>3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C</p> <p>Rear panel hinges on the longest enclosure side</p>
Base material	Aluminum
Lock	<p>Lock version: Cam</p> <p>No. of locks: 2</p> <p>Lock Insert: 3 mm double-bit</p>
Packaging unit	1 pc(s).
Net weight	11.542
Gross weight	12.149
Customs tariff number	94032080
EAN	4028177663206
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

Approvals	UL + C-UL (listed)
Explanations	<p>Declaration of conformity</p> <p>Declaration of conformity UK</p>