

Rittal – The System.

Faster – better – everywhere.



CX 6705.000

CX Pedestal

State: 2025-09-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CX 6705.000 - CX Pedestal

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.



Features

| | |
|-----------------|--|
| Model No. | CX 6705.000 |
| Version | Pedestal |
| Material | Housing: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Carbon steel, 2.5 mm |
| Surface finish | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Housing open at top Door or double door at front, with 3-point locking system Mounting panel Base Plates Lock: 3 mm double-bit |
| Dimensions | Width: 800 mm Height: 675 mm Depth: 500 mm |

Features

| | |
|--------------------------------------|--|
| Dimensions of mounting plate (W x H) | 720 mm x 625 mm |
| Number of doors | 1 |
| Door opening angle | 130° |
| IK code | IK10 |
| Note | To close the pedestal, a closure plate is required For a 2-piece console setup, a desk unit and a closure plate for the desk unit are required For a 3-piece console setup, a desk unit and console top-section are required |
| Protection category IP to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 1 NEMA 12 |
| Base material | Carbon steel |
| No. of locks | 1 |
| Lock version | 3-point locking system |
| Lock Insert | 3 mm double-bit |
| Lock | Lock version: 3-point locking system No. of locks: 1 Lock Insert: 3 mm double-bit |
| Packaging unit | 1 pc(s). |
| Net weight | 40 |
| Gross weight | 42.875 |
| Customs tariff number | 94032080 |
| EAN | 4028177983755 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |