

Rittal – The System.

Faster – better – everywhere.



DK 7507.110 FlatBox

State: 2026-05-08 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7507.110 - FlatBox

Flat-packed enclosure. For optimal access and flexible use as a wall-mounted or floor-standing enclosure.



Features

| | |
|---------------------|--|
| Model No. | DK 7507.110 |
| Version | with 19" mounting rails |
| Product description | For flexible use as a wall-mounted or floor-standing enclosure. |
| Benefits | Tool-free quick mounting System accessories on the open 19" frame |
| Material | Carbon steel Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Color | RAL 7035 |

Features

| | |
|-------------------------------------|--|
| Supply includes | Flat-packed enclosure 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door catch freely selectable Connection components for tool-free, fast assembly Grounding kit for system-compatible grounding of all enclosure parts 19" profile rails |
| Height units | 9 U |
| Dimensions | Width: 600 mm Height: 492 mm Depth: 600 mm |
| Installation height for components | 9 U |
| Load capacity | max. 450 N |
| Note | Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210° |
| Base material | Carbon steel |
| Packaging unit | 1 pc(s). |
| Net weight | 24.42 kg |
| Gross weight | 26.3 kg |
| PCF/VE (cradle-to-gate) | 102.9 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002500 |
| ETIM 8 | EC002500 |
| ECLASS 8.0 | 27180208 |
| Product description | DK FlatBox, WHD: 600x492x600 mm, 9 U, with 482.6 mm (19") mounting angles |

Approvals

Explanations

Manufacturer's declaration