Rittal – The System.

Faster - better - everywhere.





DK 7507.220 FlatBox

State: 2025-12-13 (Source: rittal.com/ca-en)



DK 7507.220 - FlatBox

Flat-packed enclosure. For optimal access and flexible use as a wall-mounted or floor-standing enclosure.







Features

Model No.	DK 7507.220
Version	with 19" mounting frame
Product description	For flexible use as a wall-mounted or floor-standing enclosure.
Benefits	Tool-free quick mounting
	System accessories on the open 19" frame
Material	Carbon steel
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	RAL 7035

© Rittal 2025

Features

Flat-packed enclosure 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door catch freely selectable Connection components for tool-free, fast assembly Grounding kit for system-compatible grounding of all enclosure parts 19" mounting frame Height units 21 U Dimensions Width: 700 mm Height: 1,025 mm Depth: 700 mm Installation height for components 21 U Load capacity max. 750 N Note Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210° Base material Carbon steel Packaging unit 1 pc(s). Net weight 49 Gross weight 51 PCF/VE (cradle-to-gate) 101.9 kg CO2 eq (Cat B) Information regarding the PCF clasos the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 ENumber Sweden E7238408 ETIM 9 EC002500 ETIM 9 EC002500		
Dimensions Width: 700 mm Height: 1,025 mm Depth: 700 mm Installation height for components 21 U Load capacity max. 750 N Note Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210° Base material Carbon steel Packaging unit 1 pc(s). Net weight 49 Gross weight 51 PCF/VE (cradle-to-gate) 201.9 kg CO2 eq (Cat B) Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 EC002500	Supply includes	 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door catch freely selectable Connection components for tool-free, fast assembly Grounding kit for system-compatible grounding of all enclosure parts
Height: 1,025 mm Depth: 700 mm Installation height for components 21 U Load capacity max. 750 N Note Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210° Base material Carbon steel Packaging unit 1 pc(s). Net weight 49 Gross weight 51 PCF/VE (cradle-to-gate) 201.9 kg CO2 eq (Cat B) Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately on class tariff number 94032080 EAN 4028177551480 ETIIM 9 EC002500	Height units	21 U
Load capacity Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210° Base material Carbon steel Packaging unit 1 pc(s). Net weight 49 Gross weight 51 PCF/VE (cradle-to-gate) Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 EC002500	Dimensions	Height: 1,025 mm
Note Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210° Base material Carbon steel Packaging unit 1 pc(s). Net weight 49 Gross weight 51 PCF/VE (cradle-to-gate) Loss product the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 ECO02500	Installation height for components	21 U
Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210° Base material Carbon steel Packaging unit 1 pc(s). Net weight 49 Gross weight 51 PCF/VE (cradle-to-gate) 201.9 kg CO2 eq (Cat B) Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately on class the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 EC002500	Load capacity	max. 750 N
Packaging unit 1 pc(s). Net weight 49 Gross weight 51 PCF/VE (cradle-to-gate) 201.9 kg CO2 eq (Cat B) Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 EC002500	Note	Max. distance between two 19" levels: Depth - 104 mm
Net weight 49 Gross weight 51 PCF/VE (cradle-to-gate) 201.9 kg CO2 eq (Cat B) Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 EC002500	Base material	Carbon steel
Gross weight 51 PCF/VE (cradle-to-gate) 201.9 kg CO2 eq (Cat B) Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 EC002500	Packaging unit	1 pc(s).
PCF/VE (cradle-to-gate) Information regarding the PCF class Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 EC002500	Net weight	49
Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 EC002500	Gross weight	51
class the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 EC002500	PCF/VE (cradle-to-gate)	201.9 kg CO2 eq (Cat B)
EAN 4028177551480 E-Number Sweden E7238408 ETIM 9 EC002500	J J	
E-Number Sweden E7238408 ETIM 9 EC002500	Customs tariff number	94032080
ETIM 9 EC002500	EAN	4028177551480
	E-Number Sweden	E7238408
ETIM 8 EC002500	ETIM 9	EC002500
	ETIM 8	EC002500

© Rittal 2025 3

Features

ECLASS 8.0 27180208

Approvals

Explanations

Manufacturer's declaration

© Rittal 2025