## Rittal – The System.

Faster - better - everywhere.






# DK 7240.200 Socket strip

State: 2025-10-31 (Source: rittal.com/ca-en)




### DK 7240.200 - Socket strip for IEC 320 Connectors

Socket strips in various designs for attaching into frames, wall-mounted distributors DK (horizontal) or between a pair of 482.6 mm (19") mounting angles.







#### **Features**

Model No.

Product description

DK 7240.200

The socket strips are available in various country-specific variants with different functional elements. Special attention has been devoted to practical, universal fastening: Variable attachment facilities have been created with an angle bracket which may be inserted in four positions. Hence, for example, the 482 mm-long socket strips may optionally be mounted on 482.6 mm (19") profile rails, the 19" mounting frame, on the enclosure frame, or in the rear section of the wall-mounted distributor. Socket strips with a length greater than 482 mm can only be mounted on the housing frame. The socket strip may be inserted into all sections with a 25 mm hole pattern, without the need for additional mounting accessories. This makes selection much easier, as well as providing additional flexibility and saving on warehousing. Provision has also been made for cable routing of the infeed, and when mounting in the 482.6 mm (19") section there is adequate space to route the infeed between the socket strip and the profile rail without kinks. The arrangement of the grounding-pin sockets at a 45° angle allows unrestricted use of angular connectors.

© Rittal 2025 2

## **Features**

Benefits	Practical, universal fastening Flexibility saves on warehousing In the 482.6 mm (19") section there is adequate space to route the infeed between the socket strip and the profile rail without kinks	
Material	Aluminum section, natural anodized Socket inserts: Polycarbonate	
Supply includes	Socket strip 2 mounting brackets Assembly components	
Version	Without switch	
Outlets	12 x Non-Heating Apparatus Socket C13	
Dimensions	Height: 44 mm Depth: 44 mm Length: 482.6 mm	
Length of connection cable	2 m	
Connection cable (type)	H05VV-F3G1.5	
Mounting dimensions	452.5 mm	
Mounting dimension tolerance	25 mm	
Rated operating voltage	250 V AC, 50 Hz	
Rated voltage	250 V AC, 50 Hz	
Rated current (max.)	16 A	
Type of connection (electrical)	Wire end ferrules	
Installation options	Components with a 25 mm pitch pattern IT wall-mounted distributor, at the rear, horizontal (adequate width provided) Enclosure frame 482.6 mm (19") level	
Note	Depending on the application, it is advisable to keep some load current in reserve to prevent nuisance tripping as a result of peak inrush currents  The mounting distance is variable across a range of 25 mm, the distance specified is the center - center distance of the holes in the mounting brackets	

© Rittal 2025

3

## Features

Standards         EN 60320-2-2           Socket color         Gray           Packaging unit         1 pc(s).           Net weight         0.8           Gross weight         0.864           Customs tariff number         85366990           EAN         4028177237537           E-Number Sweden         E7239987           ETIM 9         EC000330           ECLASS 8.0         27142604		
Packaging unit       1 pc(s).         Net weight       0.8         Gross weight       0.864         Customs tariff number       85366990         EAN       4028177237537         E-Number Sweden       E7239987         ETIM 9       EC000330	Standards	EN 60320-2-2
Net weight       0.8         Gross weight       0.864         Customs tariff number       85366990         EAN       4028177237537         E-Number Sweden       E7239987         ETIM 9       EC000330	Socket color	Gray
Gross weight         0.864           Customs tariff number         85366990           EAN         4028177237537           E-Number Sweden         E7239987           ETIM 9         EC000330	Packaging unit	1 pc(s).
Customs tariff number       85366990         EAN       4028177237537         E-Number Sweden       E7239987         ETIM 9       EC000330	Net weight	0.8
EAN       4028177237537         E-Number Sweden       E7239987         ETIM 9       EC000330	Gross weight	0.864
E-Number Sweden E7239987 ETIM 9 EC000330	Customs tariff number	85366990
ETIM 9 EC000330	EAN	4028177237537
	E-Number Sweden	E7239987
ECLASS 8.0 27142604	ETIM 9	EC000330
	ECLASS 8.0	27142604

# **Approvals**

Explanations	Declaration of conformity	
--------------	---------------------------	--

© Rittal 2025