



Rittal – The System.

Faster – better – everywhere.



DK 7391.000


Data Rack

State: 2026-01-14 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



DK 7391.000 - Data Rack

Data Rack for optimum accessibility from all sides during assembly and installation, and a high degree of mobility when twin castors are used.



Features

Model No.	DK 7391.000
Material	Profile frame, base/plinth: Carbon steel Feet: Die-cast zinc
General color	RAL 7035
Color	Profile frame, base/plinth: RAL 7035 Panel, feet: RAL 5018
Supply includes	Torsionally rigid profile frame with 482.6 mm (19") holes Stable base/plinth with integral feet, with the option of floor anchoring without base trim panels Mounting Accessories
Dimensions	Width: 550 mm Height: 1,500 mm Depth: 750 mm
Height units	31 U
Height units	31 U
Distance from the second mounting level, 50 mm hole pattern	150 - 350 mm

Features

Hole pattern between the mounting levels	50 mm
Load capacity of the 19" levels	1,500 N
Note	Order second mounting level separately
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	16.781
Gross weight	17.664
PCF/VE (cradle-to-gate)	67.1 kg CO ₂ eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177129795
E-Number Sweden	E7239646
ETIM 9	EC002507
ECLASS 8.0	27180602