


Rittal – The System.

Faster – better – everywhere.



TE 7888.875

Network enclosure TE 8000

State: 2026-02-17 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP

TE 7888.875 - Network enclosure TE 8000 Vented

IT enclosure system, suitable for dismantling, with depth-variable 482.6 mm (19") mounting frame.

Features

Model No.	TE 7888.875
Benefits	No frame structure Optimum accessibility Easily installed Interchangeable door catch
Material	Carbon steel
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
General color	RAL 7035
Color	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Carbon steel door vented (vented surface area > 67%), front with designer handle, 130° hinge, security lock 3524 E Carbon steel door vented (vented surface area > 67%), rear with 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional populating with module plates) Roof plate, incl. concealed cut-out for cable entry and optional fan 4 leveling feet, M10 (supplied loose) 4 spacers, 20 mm, to raise the roof (supplied loose) Side panels, lockable, including security lock 3524 E
Dimensions	Width: 600 mm Height: 1,200 mm Depth: 1,000 mm
Height units	24 U
Height units	24 U

Features

Mounting space to 19" level, front/
rear 80 mm / 130 mm

Distance between levels as
delivered 745 mm

Load capacity 7,000 N

Protection category IP to EN 60
529 IP 20

Base material Carbon steel

Packaging unit 1 pc(s).

Net weight 69

Gross weight 70

Customs tariff number 94032080

EAN 4028177801509

E-Number Sweden E7282506

ETIM 9 EC002499

ECLASS 8.0 27180207

Approvals

Explanations Declaration of conformity