

# Rittal – The System.

Faster – better – everywhere.



## DK 7955.201

## PDU international, metered version

State: 2025-12-19 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7955.201 - PDU international, metered version

Compact basic power distributor with power measurement for each phase or input. Quick overview of the power requirements for the entire IT rack. Distributed power up to 22 kW

## Features

Model No.	DK 7955.201
Version	PDU, metered
Product description	Energy measurement for each phase, i.e., power requirement for a whole IT rack. Due to the compact PDU, all IT racks can easily be equipped with a professional power distribution system. The compact design allows for simple mounting - with the TS IT rack, mounting can be carried out without tools. The OLED display indicates the energy consumption. An integrated web server enables direct network connection with comprehensive user management. The redundant power supply originates from all phases and also via an existing Power-over-Ethernet network. The PDU offers extensive monitoring functions. Measurement accuracy of 1% guarantees a high level of reliability.
Material	Aluminum section, black anodized
Dimensions	Width: 44 mm Depth: 62 mm Length: 710 mm
Number of sockets and type	12 x C13
Outlets	12 x Non-Heating Apparatus Socket C13
Rated current (max.)	16 A
Infeeds	Qty.: 1 Phases per infeed: 1~
Length of connection cable	3 m
Type of connection (electrical)	C20
Guidelines	EMC Directive 2014/30/EU Low-Voltage Directive 2014/35/EU
Standards	EN 60950-1

# Features

Operating temperature range	0 °C...45 °C
Ambient humidity (non-condensing)	10...95 %
Storage temperature range	-25 °C...70 °C
Suitable for	Enclosure type: TS IT: $\geq 1,200$ mm
Packaging unit	1 pc(s).
Net weight	1.9
Gross weight	3
Customs tariff number	85366990
EAN	4028177685277
ETIM 9	EC002762
ECLASS 8.0	27142604