

Rittal – The System.

Faster – better – everywhere.



DK 7501.000 VerticalBox

State: 2024-05-11 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7501.000 - VerticalBox

Compact 19" enclosure for small networks that may be used for wall-mounted, under-desk or desktop applications.

Features

Model No.	DK 7501.000
Product description	Compact 19" enclosure for small networks.
Benefits	May be used as wall-mounted, under-desk or desktop applications Free access from three sides for interior installation Passive ventilation with vent slots Rear panel prepared to accommodate a fan Freely selectable door catch Space-saving, vertical mounting of 19" installation components at the side
Material	Carbon steel Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	RAL 7035
Supply includes	Housing with viewing door Side panels (1 x fixed, 1 x slot-in) with vent slots Knockouts for cable entry via roof or base Slot-in rear panel with knockouts for cable entry and fan accommodation 19" mounting level, 5 U, horizontal front and rear, depth-variable, distance between levels 434 – 489 mm Security lock 12321 on the door, side and rear panel 4 plastic feet, self-adhesive
Dimensions	Width: 300 mm Height: 540 mm Depth: 600 mm
Installation height for components	5 U
Base material	Carbon steel
Packaging unit	1 pc(s).

Features

Weight/packaging unit	17.04 kg
Customs tariff number	94032080
EAN	4028177625426
ETIM 7.0	EC002500
ECLASS 8.0	27180208

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------