## Rittal – The System.

Faster - better - everywhere.






# DK 7507.000 FlatBox

State: 2025-12-12 (Source: rittal.com/ca-en)



### DK 7507.000 - FlatBox

Flat-packed enclosure. For optimal access and flexible use as a wall-mounted or floor-standing enclosure.







#### **Features**

Model No.	DK 7507.000
Version	with 19" mounting rails
Product description	For flexible use as a wall-mounted or floor-standing enclosure.
Benefits	Tool-free quick mounting
	System accessories on the open 19" frame
Material	Carbon steel
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	RAL 7035

© Rittal 2025

#### **Features**

Supply includes	Flat-packed enclosure  1 wall section  2 basic supports  2 roof/base plates, with cut-outs for cable entry via brush strips  2 side panels, lockable  1 glazed door, lockable, security lock 3524 E, door catch freely selectable  Connection components for tool-free, fast assembly  Grounding kit for system-compatible grounding of all enclosure parts  19" profile rails
Height units	6 U
Dimensions	Width: 600 mm Height: 358 mm Depth: 400 mm
Installation height for components	6 U
Load capacity	max. 300 N
Note	Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210°
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	16.739
Gross weight	17.66
PCF/VE (cradle-to-gate)	68 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177551398
E-Number Sweden	E7238400
ETIM 9	EC002500
ETIM 8	EC002500

© Rittal 2025

3

## Features

ECLASS 8.0 27180208

# **Approvals**

Explanations

Manufacturer's declaration

© Rittal 2025