

Rittal – The System.

Faster – better – everywhere.



WM 8017.568

WM wall-mounted disconnect enclosure

State: 2026-05-22 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8017.568 - WM wall-mounted disconnect enclosure

These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8017.568
Product description	These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.
Material	Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel, zinc-plated
Surface finish	Dipcoat-primed and powder-coated, textured paint
Color	RAL 7035
Supply includes	Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes Flange door with universal disconnect cutout 2-point latching L-Handle
Dimensions	Width: 825 mm Height: 900 mm Depth: 250 mm

Features

Dimensions of mounting plate (W x H)	704 mm x 870 mm
--------------------------------------	-----------------

Protection category NEMA	NEMA 4 UL Type 4/3R/12
--------------------------	---------------------------

Material thickness - door	2 mm
---------------------------	------

Material thickness - enclosure	2 mm
--------------------------------	------

Material thickness – mounting plate	3 mm
-------------------------------------	------

Packaging unit	1 pc(s).
----------------	----------

Net weight	132 lb
------------	--------

Gross weight	132.275 lb
--------------	------------

Customs tariff number	8538100000
-----------------------	------------

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------

Explanations	Declaration of conformity
--------------	---------------------------