Rittal – The System.

Faster – better – everywhere.





DK 7507.020 FlatBox

State: 2025-12-11 (Source: rittal.com/ca-en)



DK 7507.020 - FlatBox

Flat-packed enclosure. For optimal access and flexible use as a wall-mounted or floor-standing enclosure.







Features

Model No.	DK 7507.020
Version	with 19" mounting frame
Benefits	Tool-free quick mounting
	System accessories on the open 19" frame
Material	Carbon steel
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	RAL 7035
Supply includes	Flat-packed enclosure
	1 wall section
	2 basic supports
	2 roof/base plates, with cut-outs for cable entry via brush strips
	2 side panels, lockable
	1 glazed door, lockable, security lock 3524 E, door catch freely
	selectable
	Connection components for tool-free, fast assembly
	Grounding kit for system-compatible grounding of all enclosure
	parts
	19" mounting frame

© Rittal 2025

Features

Height units	12 U
Dimensions	Width: 600 mm Height: 625 mm Depth: 400 mm
Installation height for components	12 U
Load capacity	max. 600 N
Note	Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210°
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	24.828
Gross weight	25.246
PCF/VE (cradle-to-gate)	100.8 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177551411
E-Number Sweden	E7238403
ETIM 9	EC002500
ETIM 8	EC002500
ECLASS 8.0	27180208

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------

© Rittal 2025 3