

Rittal – The System.

Faster – better – everywhere.



JB 8018.119 JB Junction box

State: 2026-06-13 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



JB 8018.119 - JB Junction box Carbon steel

The JB enclosure offers protection for dense wiring and sensitive small instruments. These hinged cover junction boxes combine the advantages of the AE and KL series at an economical cost. Features include 180 degree hinge and slotted insert quarter turn latch. Foamed-in-place gasket and a knife-edge perimeter add extra protection.



Features

Model No.	JB 8018.119
Material	Housing and door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	180° hinge Housing with door
Material thickness - door	1.5 mm
Material thickness - enclosure	1.5 mm
Material thickness – mounting plate	1.5 mm
Position door catch	left
Dimensions	Width: 100 mm Height: 100 mm Depth: 75 mm
Protection category IP to IEC 60529	IP 66

Features

Protection category NEMA	NEMA 4
Packaging unit	1 pc(s).
Net weight	2.101 lb
Gross weight	2.205 lb
Customs tariff number	8538100000

Approvals

Approvals	UL
Explanations	Declaration of conformity