

# Rittal – The System.

Faster – better – everywhere.



## WM 8018.700

## WM wall-mounted enclosure

State: 2026-03-13 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# WM 8018.700 - WM wall-mounted enclosure stainless steel, with Roof Slope

The WMS slope top wallmount enclosure is designed for any environment that requires frequent washdowns. The 20 degree overhanging sloped roof prevents water from accumulating on top of the enclosure and door opening.

## Features

|                                      |  |
|--------------------------------------|--|
| Model No.                            | WM 8018.700  |
| Material                             | Door: Stainless steel, all-round foamed-in PU seal<br>Housing and door: Stainless steel 1.4301 (AISI 304)<br>Mounting plate: Carbon steel, zinc-plated |
| Surface finish                       | Brushed  |
| Supply includes                      | Housing with door<br>Door hinged on left<br>Mounting plate<br>Wall mounting blind-nuts<br>20° overhanging slope top                                    |
| Dimensions                           | Width: 600 mm<br>Height: 595 mm<br>Depth: 300 mm   |
| Dimensions of mounting plate (W x H) | 549 mm x 570 mm  |
| Protection category NEMA             | NEMA 4X  |
| Material thickness - door            | 2 mm   |
| Material thickness - enclosure       | 1.5 mm   |
| Material thickness – mounting plate  | 2.5 mm   |
| Lock                                 | Lock version: Quarter turn   |
| Packaging unit                       | 1 pc(s).   |
| Net weight                           | 65 lb  |

## Features

---

|                       |            |
|-----------------------|------------|
| Gross weight          | 65 lb      |
| Customs tariff number | 8538100000 |

---

## Approvals

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|