

Rittal – The System.

Faster – better – everywhere.



TE 7888.430

Network enclosure TE 8000

State: 2026-02-01 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TE 7888.430 - Network enclosure TE 8000

TE 8000 IT enclosure with glazed door, designed for individual interior installation.

Features

Model No.	TE 7888.430
Version	with side panels
Benefits	No frame structure Optimum accessibility Easily installed Interchangeable door catch
Material	Carbon steel Viewing door: Single-pane safety glass, 3 mm
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
General color	RAL 7035
Color	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, incl. 130° hinge, design handle and security lock 3524 E Carbon steel door at the rear, including 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional populating with module plates) Roof plate, incl. concealed cut-out for cable entry and optional fan 4 leveling feet, M10 (supplied loose) 4 spacers, 20 mm, to raise the roof (supplied loose) Side panels, lockable, including security lock 3524 E
Dimensions	Width: 600 mm Height: 1,200 mm Depth: 600 mm
Height units	24 U
Height units	24 U

Features

Mounting space to 19" level, front/
rear 30 mm / 30 mm /

Distance between levels as
delivered 495 mm

Load capacity 4,000 N

Protection category IP to EN 60
529 IP 20

Base material Carbon steel

Packaging unit 1 pc(s).

Net weight 54

Gross weight 56

EAN 4028177801400

E-Number Sweden E7239996

ETIM 9 EC002499

ECLASS 8.0 27180207

Approvals

Explanations Declaration of conformity