

Rittal – The System.

Faster – better – everywhere.



TE 7888.430

Network enclosure TE 8000

State: 2026-06-21 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7888.430 - Network enclosure TE 8000

TE 8000 IT enclosure with glazed door, designed for individual interior installation.

Features

Model No.	TE 7888.430
Version	with side panels
Benefits	No frame structure Optimum accessibility Easily installed Interchangeable door catch
Material	Carbon steel Viewing door: Single-pane safety glass, 3 mm
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
General color	RAL 7035
Color	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, incl. 130° hinge, design handle and security lock 3524 E Carbon steel door at the rear, including 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional populating with module plates) Roof plate, incl. concealed cut-out for cable entry and optional fan 4 leveling feet, M10 (supplied loose) 4 spacers, 20 mm, to raise the roof (supplied loose) Side panels, lockable, including security lock 3524 E
Dimensions	Width: 600 mm Height: 1,200 mm Depth: 600 mm
Height units	24 U
Height units	24 U

Features

Mounting space to 19" level, front/ rear	30 mm / 30 mm /
Distance between levels as delivered	495 mm
Load capacity	4,000 N
Protection category IP to EN 60 529	IP 20
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	54 kg
Gross weight	56 kg
Customs tariff number	94032080
ETIM 9	EC002499
ECLASS 8.0	27180207
Product description	TE Network enclosure TE 8000, WHD: 600x1200x600 mm, 24 U, With glazed door

Approvals

Explanations

Declaration of conformity