


**Rittal – The System.**

Faster – better – everywhere.



**TE 7888.530**

**Network enclosure TE 8000**

State: 2026-02-01 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# TE 7888.530 - Network enclosure TE 8000

TE 8000 IT enclosure with glazed door, designed for individual interior installation.

## Features

Model No.	TE 7888.530
Version	with side panels
Benefits	No frame structure Optimum accessibility Easily installed Interchangeable door catch
Material	Carbon steel Viewing door: Single-pane safety glass, 3 mm
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
General color	RAL 7035
Color	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, incl. 130° hinge, design handle and security lock 3524 E Carbon steel door at the rear, including 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional populating with module plates) Roof plate, incl. concealed cut-out for cable entry and optional fan 4 leveling feet, M10 (supplied loose) 4 spacers, 20 mm, to raise the roof (supplied loose) Side panels, lockable, including security lock 3524 E
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm
Height units	42 U
Height units	42 U

# Features

---

Mounting space to 19" level, front/  
rear 130 mm / 130 mm /

---

Distance between levels as  
delivered 495 mm

---

Load capacity 4,000 N

---

Protection category IP to EN 60  
529 IP 20

---

Base material Carbon steel

---

Packaging unit 1 pc(s).

---

Net weight 104

---

Gross weight 106

---

EAN 4028177801462

---

E-Number Sweden E7282502

---

ETIM 9 EC002499

---

ECLASS 8.0 27180207

---

# Approvals

---

Explanations Declaration of conformity