


# Rittal – The System.

Faster – better – everywhere.



## TE 7888.892

## Network enclosure TE 8000

State: 2026-02-03 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))



FRIEDHELM LOH GROUP

# TE 7888.892 - Network enclosure TE 8000 Vented

IT enclosure system, suitable for dismantling, with depth-variable 482.6 mm (19") mounting frame.

## Features

Model No.	TE 7888.892
Benefits	No frame structure Optimum accessibility Easily installed Interchangeable door catch
Material	Carbon steel
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
General color	RAL 7035
Color	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Carbon steel door vented (vented surface area > 67%), front with designer handle, 130° hinge, security lock 3524 E Carbon steel door vented (vented surface area > 67%), rear with 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional populating with module plates) Roof plate, incl. concealed cut-out for cable entry and optional fan 4 leveling feet, M10 (supplied loose) 4 spacers, 20 mm, to raise the roof (supplied loose) Baying kit
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 1,000 mm
Height units	42 U
Height units	42 U

# Features

---

Mounting space to 19" level, front/  
rear 80 mm / 130 mm

---

Distance between levels as  
delivered 745 mm

---

Load capacity 7,000 N

---

Protection category IP to EN 60  
529 IP 20

---

Base material Carbon steel

---

Packaging unit 1 pc(s).

---

Net weight 78

---

Gross weight 81

---

EAN 4028177801523

---

E-Number Sweden E7282508

---

ETIM 9 EC002499

---

ECLASS 8.0 27180207

---

# Approvals

---

Explanations Declaration of conformity