

Rittal – The System.

Faster – better – everywhere.



VX 8619.410

Cable clamp rail

State: 2026-01-27 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

VX 8619.410 - Cable clamp rail Mounting angle for VX, TS, VX SE, PC & VX base/plinth system

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

Features

Model No.	VX 8619.410
Product description	Provides strain relief for cable entries. Depth-variable mounting in a 25 mm hole pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options VX	In enclosure width 600 mm, in the base
Installation options VX SE	In enclosure width 600 mm, in the base
Installation options AX	In enclosure width 600 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
Installation options AX stainless steel	In housing width 600 mm, in conjunction with the rail for interior fitting with base configuration rail
Installation options PC	In enclosure width 600 mm, in the base
Installation options IW	In enclosure width 600 mm, in the base
Installation options VX Base	In base/plinth width/depth 600 mm, in conjunction with retaining/ spacer piece
Installation options VX base/plinth, stainless steel	In base/plinth width 600 mm, in conjunction with a M8 nut
Installation options AX Base	In base/plinth width 600 mm
Suitable for	AX base/plinth system VX base system VX base/plinth system, stainless steel

Features

Dimensions	Length: 554 mm
Suitable for	Enclosure type: VX VX SE PC IW AX CX Pedestal CX One-Piece Console Width: = 600 mm
Suitable for width	600 mm
Packaging unit	2 pc(s).
Net weight	2.8
Gross weight	3.161
Customs tariff number	83024900
EAN	4028177921931
ETIM 9	EC000322
ECLASS 8.0	27400604