

# Rittal – The System.

Faster – better – everywhere.



## TS 8008.530

## Baying systems TS 8

State: 2025-07-18 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8008.530 - Baying systems TS 8

Due to its symmetrical profile in terms of width and depth, the TS 8 baying system, made from carbon steel, saves considerable space and facilitates easy internal installation. It also allows a baying arrangement on all sides. In addition, the integrated, automatic potential equalization of all enclosure panels and the triple machining of the surface ensures maximum safety.

## Features

Model No.	TS 8008.530
Material	Enclosure frame: Carbon steel, 1.5 mm Roof: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Enclosure frame Door(s) Right-hand door catch on single-door enclosures may be swapped to the left Roof plate Rear panel 4 eyebolts Lock: 3 mm double-bit Gland plate Mounting plate 2 TS punched rails, 18 x 38 mm
Dimensions	Width: 1,000 mm Height: 2,000 mm Depth: 800 mm
Protection category IP to EN 60529	IP 55
Protection category NEMA	NEMA 1 NEMA 12

# Features

Type rating according to UL 50E	Type 1 Type 12
IK code	IK09
Number of doors	1
Base material	Carbon steel
Packaging unit	1 pc(s).
Gross weight	355
Customs tariff number	7326908688
UPC-Code	81068
ECLASS 8.0	27180101

# Approvals

Approvals	Bureau Veritas UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK