


Rittal – The System.

Faster – better – everywhere.



VX 8620.001

**Base/plinth corner pieces with
base/plinth trim panels, front and
rear, 100 mm**

State: 2026-06-21 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8620.001 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm for VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Base/plinth corner pieces with molded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for best access to the screw-fastening point can be covered using bay and corner covers.

Features

| | |
|-----------------------|---|
| Model No. | VX 8620.001 |
| Product description | Base/plinth corner pieces with molded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for best access to the screw-fastening point can be covered using bay and corner covers. |
| Material | Base/plinth corner piece: Carbon steel Base/plinth trim panels, front/rear: Carbon steel Corner and baying covers: Plastic |
| Color | RAL 9005 |
| Supply includes | 4 x base/plinth corner pieces, 100 mm high 4 x corner covers 1 x baying cover 2 x base/plinth trim panels, front/rear, 100 mm high Assembly components |
| Note | Base/plinth trim panels, on the side for closing off a base/plinth unit, for additional stabilization of the bases/plinths to one another, or for interior installation of the bases/plinths |
| Dimensions | Height: 100 mm |
| Suitable for | Enclosure type: VX Width: = 400 mm |
| Weight/packaging unit | 3.32 kg |

Features

| | |
|-----------------------|---|
| Packaging unit | 2 pc(s). |
| Net weight | 3.12 kg |
| Customs tariff number | 94039910 |
| ECLASS 8.0 | 27182003 |
| Product description | VX Base/plinth corner piece, with base/plinth trim panel, front and rear, H: 100 mm, for W: 400 mm, sheet steel |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|