
Rittal - The System.

Faster – better – everywhere.





VX 8620.001

Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm

State: 2025-10-23 (Source: rittal.com/ca-en)

NCLOSURES

OWER DISTRIBUTION

LIMATE CONTROL

T INFRASTRUCTURI

SOFTWARE & SERVICES

VX 8620.001 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm for VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Base/plinth corner pieces with molded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for best access to the screw-fastening point can be covered using bay and corner covers.

Features

Model No.	VX 8620.001
Product description	Base/plinth corner pieces with molded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for best access to the screw-fastening point can be covered using bay and corner covers.
Material	Base/plinth corner piece: Carbon steel
	Base/plinth trim panels, front/rear: Carbon steel
	Corner and baying covers: Plastic
Color	RAL 9005
Supply includes	4 x base/plinth corner pieces, 100 mm high
	4 x corner covers
	1 x baying cover
	2 x base/plinth trim panels, front/rear, 100 mm high
	Assembly components
Note	Base/plinth trim panels, on the side for closing off a base/plinth
	unit, for additional stabilization of the bases/plinths to one another,
	or for interior installation of the bases/plinths
Dimensions	Height: 100 mm
Suitable for	Enclosure type: VX
	Width: = 400 mm
Weight/packaging unit	3.32 kg

© Rittal 2025 2

Features

Packaging unit	2 pc(s).
Net weight	3.12
Customs tariff number	94039910
EAN	4028177922006
E-Number Sweden	E3465047
ECLASS 8.0	27182003

Approvals

Approvals UL + C-UL - FTTA