## Rittal - The System.

Faster – better – everywhere.





# WM 8018.708 WM wall-mounted enclosure

State: 2025-12-02 (Source: rittal.com/ca-en)



# WM 8018.708 - WM wall-mounted enclosure stainless steel, with Roof Slope

The WMS slope top wallmount enclosure is designed for any environment that requires frequent washdowns. The 20 degree overhanging sloped roof prevents water from accumulating on top of the enclosure and door opening.

#### **Features**

Model No.	WM 8018.708
Material	Door: Stainless steel, all-round foamed-in PU seal Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door Door hinged on left Mounting plate Wall mounting blind-nuts 20° overhanging slope top
Dimensions	Width: 900 mm Height: 1,195 mm Depth: 400 mm
Dimensions of mounting plate (W x H)	840 mm x 1,155 mm
Protection category NEMA	NEMA 4X
Material thickness - door	2 mm
Material thickness - enclosure	2 mm
Material thickness – mounting plate	2.5 mm
Lock	Lock version: 3-point locking system
Packaging unit	1 pc(s).
Net weight	194.998

© Rittal 2025 2

### **Features**

Gross weight	194.998
Customs tariff number	7326908688
UPC-Code	84055

# **Approvals**

Explanations Declaration of conformity

© Rittal 2025 3