Rittal – The System.

Faster – better – everywhere.





TS 8206.500 Baying systems TS 8

State: 2025-11-25 (Source: rittal.com/ca-en)



TS 8206.500 - Baying systems TS 8

Due to its symmetrical profile in terms of width and depth, the TS 8 baying system, made from carbon steel, saves considerable space and facilitates easy internal installation. It also allows a baying arrangement on all sides. In addition, the integrated, automatic potential equalization of all enclosure panels and the triple machining of the surface ensures maximum safety.



Features

TS 8206.500
Enclosure frame: Carbon steel, 1.5 mm
Roof: Carbon steel, 1.5 mm
Door: Carbon steel, 2.0 mm
Rear wall: carbon steel, 1.5 mm
Base plates: Carbon steel, 1.5 mm
Mounting panel: Carbon steel, 3.0 mm
Enclosure frame: Dipcoat-primed
Door, roof and rear panel: Dipcoat-primed, powder-coated on the
outside, textured paint
Mounting plate and base plates: Zinc-plated
RAL 7035

© Rittal 2025 2

Features

Supply includes	Enclosure frame
	Door(s)
	Right-hand door catch on single-door enclosures may be swapped
	to the left
	Roof plate
	Rear panel
	4 eyebolts
	Lock: 3 mm double-bit
	Base Plates
	Mounting panel
	2 TS punched rails, 18 x 38 mm 2 support strips fitted in the enclosure depth
Dimensions	
	Width: 1,200 mm
	Height: 2,000 mm
	Depth: 600 mm
Dimensions of mounting plate (W x H)	1,099 mm x 1,896 mm
Protection category IP to EN 60 529	IP 55
Protection category NEMA	NEMA 1
	NEMA 12
Type rating according to UL 50E	Type 1
	Type 12
	IK09
Number of doors	2
2 supportstrips in depth	Yes
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	184.87
Gross weight	194.6
Customs tariff number	94032080
	4028177250888
EAN	4020177230000

© Rittal 2025 3

Features

Approvals

Approvals	Bureau Veritas Lloyds Register of Shipping UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK

© Rittal 2025