


Rittal – The System.

Faster – better – everywhere.



VX 8620.072

Base/plinth trim panels, side, 100 mm, stainless steel

State: 2025-08-10 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8620.072 - Base/plinth trim panels, side, 100 mm, stainless steel For VX base/plinth systems

Stainless steel base/plinth trim panels are used depth-wise for laterally closing a base/plinth unit or for the inner fitting of aligned base/plinths. The 100 mm high trim panels can also be used and combined in 200 mm high base/plinths.

Features

| | |
|---------------------------------|---|
| Model No. | VX 8620.072 |
| Product description | For side completion of a base/plinth unit and for additional stabilization or the interior installation of baying bases. One 200 mm high or two 100 mm high trim panels can optionally be used to 200 mm high base/plinths. |
| Material | Stainless steel 1.4301 (AISI 304) |
| Surface finish | Brushed, grain 400 |
| Supply includes | Assembly components |
| Note | The components of the first generation base/plinth system cannot be combined with the components of the second generation base/plinth system |
| Dimensions | Height: 100 mm |
| Suitable for | Depth: = 600 mm |
| Type rating according to UL 50E | Type 1 Type 3R Type 4 Type 4X Type 12 |
| Weight/package unit | 2.8 kg |
| Packaging unit | 2 pc(s). |
| Net weight | 1.72 |
| Gross weight | 1.82 |
| Customs tariff number | 94039910 |

Features

| | |
|------------|---------------|
| EAN | 4028177922396 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|