Rittal – The System.

Faster – better – everywhere.





TS 8406.510 Baying systems TS 8

State: 2025-11-25 (Source: rittal.com/ca-en)



TS 8406.510 - Baying systems TS 8

Due to its symmetrical profile in terms of width and depth, the TS 8 baying system, made from carbon steel, saves considerable space and facilitates easy internal installation. It also allows a baying arrangement on all sides. In addition, the integrated, automatic potential equalization of all enclosure panels and the triple machining of the surface ensures maximum safety.





Features

Model No.	TS 8406.510
Material	Enclosure frame: Carbon steel, 1.5 mm
	Roof: Carbon steel, 1.5 mm
	Door: Carbon steel, 2.0 mm
	Rear wall: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed
	Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Enclosure frame
	Door(s)
	Right-hand door catch on single-door enclosures may be swapped
	to the left
	Roof plate
	Rear panel
	4 eyebolts
	Lock: 3 mm double-bit
	2 support strips fitted in the enclosure depth
Dimensions	Width: 400 mm
	Height: 2,000 mm
	Depth: 600 mm

© Rittal 2025 2

Features

Protection category IP to EN 60 529	IP 55 in conjunction with side panels and gland plates
Protection category NEMA	NEMA 12 in conjunction with side panels and gland plates
Type rating according to UL 50E	Type 1 Type 12
IK code	IK09
Number of doors	1
2 supportstrips in depth	Yes
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	51.7
Gross weight	55.6
EAN	4028177357273
ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas Lloyds Register of Shipping UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK

© Rittal 2025 3