

# Rittal – The System.

Faster – better – everywhere.



## TS 8609.040 Divider panel

State: 2025-07-13 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8609.040 - Divider panel for TS

To shield individual enclosure cells. The symmetry of the frame system means the divider panel can also be used at the rear.



## Features

Model No.	TS 8609.040
Product description	To shield individual enclosure cells. All-round, double edging for stability and to accommodate the seal. The symmetry of the enclosure frame means divider panels of the appropriate dimensions can also be fitted at the rear.
Applications	Notches in the corners and half-way up the sides permit the use of angular baying brackets and baying brackets, even with a divider panel fitted.
Material	Carbon steel, 1.5 mm
Surface finish	Zinc-plated
Supply includes	Assembly components
Suitable for	Enclosure type: TS 8 Height: = 2,000 mm Depth: = 400 mm
Installation options	Mounted on the outer mounting level The inner level remains free for further expansion
Mounting tip	The divider panel may also be fitted at the rear. This allows, e.g. frequency converters for heat dissipation to be installed in a divider panel with the cooling units facing outwards and protected/ concealed with a cover.

# Features

Protection category IP to IEC 60529	IP 54
Packaging unit	1 pc(s).
Net weight	8.471
Gross weight	8.905
Customs tariff number	94039910
EAN	4028177208735
ETIM 9	EC002525
ECLASS 8.0	27182102