## Rittal - The System.

Faster – better – everywhere.





# VX 8660.009

Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 2025-12-14 (Source: rittal.com/ca-en)

NCLOSURE

OWER DISTRIBUTION

LIMATE CONTROL

T INFRASTRUCTURI

SOFTWARE & SERVICES

# VX 8660.009 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, carbon steel

Base/plinth corner pieces with trim panels for flexible cable entry.





#### **Features**

Model No.	VX 8660.009
Benefits	Reliable - very high stability of the base
	Flexible – numerous interior expansion options with the VX
	accessories
	Simple – flush finish between the baying points
Material	Base/plinth corner piece: Carbon steel
	Base/plinth trim panels, front/rear: Carbon steel
	Corner and baying covers: Plastic
Color	RAL 9005
Supply includes	4 x corner covers
	Assembly components
	4 x base/plinth corner pieces, 100 mm high
	2 x base/plinth trim panels, front/rear, 100 mm high
Note	Base/plinth trim panels, on the side for closing off a base/plinth
	unit, for additional stabilization of the bases/plinths to one another
	or for interior installation of the bases/plinths
Dimensions	Height: 100 mm

© Rittal 2025 2

### **Features**

Suitable for	Enclosure type: VX
	VXIT
	VX SE
	TX CableNet
	TS TS IT
	PC
	IW
	CX
	Width: = 1,800 mm
Type rating according to UL 50E	Type 1
	Type 12
Weight/packaging unit	9.55 kg
Packaging unit	2 pc(s).
Net weight	9.546
Gross weight	9.55
PCF/VE (cradle-to-gate)	36.4 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177978102
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

## Approvals

Approvals	UL + C-UL - FTTA
Explanations	PCF-declaration

© Rittal 2025 3