## Rittal - The System.

Faster - better - everywhere.





# TS 8612.050 TS System Chassis 17 x 73 mm

State: 2025-12-10 (Source: rittal.com/ca-en)



## TS 8612.050 - TS System Chassis 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.







#### **Features**

Model No.	TS 8612.050
Version	For the inner mounting level and for mounting on doors
Product description	For universal skeleton structures or partial assembly. Simply locate onto the punchings and secure.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	490 mm
Suitable for door width	600 mm
Installation options	On the vertical TS, VX SE enclosure profile: on the inner mounting level, all-round, height-offset On the horizontal VX SE enclosure section top, in depth In TP via rails for interior installation: in width, for inner mounting level As installation kit for device bases in TS, VX SE, simply hook in and secure
Mounting tip	The rail for interior installation is required when installing in TP

© Rittal 2025

### **Features**

Suitable for	Enclosure type: VX SE
	TP
	PC
	IW
	Width/depth: 500 mm
Packaging unit	4 pc(s).
Net weight	2.008
Gross weight	2.199
PCF/VE (cradle-to-gate)	8.6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177212084
ETIM 9	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3