

Rittal – The System.

Faster – better – everywhere.



VX 8660.062

Base/plinth corner piece with base/
plinth trim panel, front and rear for
VX base/plinth system, stainless
steel



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

VX 8660.062 - Base/plinth corner piece with base/plinth trim panel, front and rear for VX base/plinth system, stainless steel new version/design

Base/plinth corner pieces with front and rear panel. Large openings in the base/plinth corner piece for best access to the screw-fastening point. Seamless baying.



Features

| | |
|-----------------|--|
| Model No. | VX 8660.062 |
| Material | Base/plinth corner piece: Stainless steel 1.4301 (AISI 304) Base/plinth trim panels, front/rear: Stainless steel 1.4301 (AISI 304) Cover caps: ABS |
| Surface finish | Brushed, grain 400 |
| Supply includes | Assembly components 4 x base/plinth corner pieces 4 cover caps 1 base/plinth trim panel, front/rear, 200 mm 2 x base/plinth trim panels, front/rear, 100 mm high |
| Note | Base/plinth side trim panels are required to finish a base/plinth unit and together provide additional stabilization of the base/plinth. The cover caps included in the delivery scope can be replaced with stainless steel cover caps for the VX base/plinth system. The components of the first generation base/plinth system cannot be combined with the components of the second generation base/plinth system |
| Dimensions | Height: 200 mm |

Features

| | |
|---------------------------------|--|
| Suitable for | Enclosure type: VX VX SE TS PC Width: = 1,000 mm |
| Type rating according to UL 50E | Type 1 Type 3R Type 4 Type 4X Type 12 |
| Packaging unit | 2 pc(s). |
| Net weight | 9 kg |
| Gross weight | 9.555 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000721 |
| ETIM 8 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | VX base/plinth corner piece with base trim panel, front and rear, H: 200 mm, for W: 1000 mm, stainless steel, 1.4301 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|