

# Rittal – The System.

Faster – better – everywhere.



VX 8660.063

Base/plinth corner piece with base/  
plinth trim panel, front and rear for  
VX base/plinth system, stainless  
steel



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

# VX 8660.063 - Base/plinth corner piece with base/plinth trim panel, front and rear for VX base/plinth system, stainless steel new version/design

Base/plinth corner pieces with front and rear panel. Large openings in the base/plinth corner piece for best access to the screw-fastening point. Seamless baying.



## Features

Model No.	VX 8660.063
Material	Base/plinth corner piece: Stainless steel 1.4301 (AISI 304) Base/plinth trim panels, front/rear: Stainless steel 1.4301 (AISI 304) Cover caps: ABS
Surface finish	Brushed, grain 400
Supply includes	Assembly components 4 x base/plinth corner pieces 4 cover caps 1 base/plinth trim panel, front/rear, 200 mm 2 x base/plinth trim panels, front/rear, 100 mm high
Note	Base/plinth side trim panels are required to finish a base/plinth unit and together provide additional stabilization of the base/plinth. The cover caps included in the delivery scope can be replaced with stainless steel cover caps for the VX base/plinth system. The components of the first generation base/plinth system cannot be combined with the components of the second generation base/plinth system
Dimensions	Height: 200 mm

# Features

---

Suitable for	Enclosure type: VX VX SE TS PC Width: = 1,200 mm
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
Packaging unit	2 pc(s).
Net weight	10.98 kg
Gross weight	10.989 kg
Customs tariff number	94039910
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003
Product description	VX base/plinth corner piece with base trim panel, front and rear, H: 200 mm, for W: 1,200 mm, stainless steel, 1.4301

---

# Approvals

---

Approvals	UL + C-UL - FTTA
-----------	------------------