


Rittal – The System.

Faster – better – everywhere.



TS 8802.065

Section for cable entry, rear

State: 2026-01-31 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

TS 8802.065 - Section for cable entry, rear for TS, TP

Inserted in base opening.

Features

| | |
|--------------------------------------|---|
| Model No. | TS 8802.065 |
| Product description | To seal the cable entry on the base opening. |
| Benefits | Particularly well-suited to cables with identical cross-sections When installing the mounting plate in the rearmost position, the cables may be routed directly without large bending radii. |
| Technical specifications | Foam rubber cable clamping profile: Cross-section: 30 x 25 mm |
| Applications | Mount directly on the base opening/base tray and base plate |
| Material | Extruded aluminum section Foam rubber cable clamping profile: PU foam |
| Supply includes | Plug-in sections, incl. foam rubber clamp strip |
| Note | 2 pc(s). are sufficient for one base opening up to an enclosure width of 800 mm From an enclosure width of 1,000 mm, two base openings are provided. 4 units per enclosure may be fitted |
| Suitable for | Enclosure type: TS: = 600 mm Enclosure type: TP |
| Protection category IP to IEC 60 529 | IP 55 if correctly installed |
| Packaging unit | 2 pc(s). |
| Net weight | 0.208 |
| Gross weight | 0.21 |
| Customs tariff number | 76042990 |
| EAN | 4028177496354 |
| ETIM 9 | EC002624 |
| ECLASS 8.0 | 27189265 |