

Rittal – The System.

Faster – better – everywhere.



VX 8617.100

System chassis 23 x 64 mm

State: 2026-05-22 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8617.100 - System chassis 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable and individual interior fitting of the enclosure frame on the inner mounting level and for installation in compact control enclosures.



Features

| | |
|---|--|
| Model No. | VX 8617.100 |
| Product description | For variable and individual interior fitting of the enclosure frame on the inner mounting level and for installation in compact control enclosures. |
| Benefits | Simply place in the system punchings and screw-fasten System punchings on all four sides With slots at the top and bottom for cage nuts, for attaching your own components via metric screws |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly components |
| Installation options VX SE | In enclosure depth 300 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility |
| Installation options AX | In enclosure width/height 300 mm, in conjunction with rail for interior installation AX and base configuration rail for AX |
| Installation options AX stainless steel | In enclosure width/height 300 mm, in conjunction with the base configuration rail |

Features

| | |
|------------------------------|---|
| Installation options VX Base | In base/plinth width/depth 300 mm on the base/plinth panels, in conjunction with base/plinth installation bracket In base/plinth width/depth 400 mm when mounting on the base/plinth corner pieces |
| Suitable for | Enclosure type: VX IT VX SE AX Suitable for width or height or depth: 300 mm |
| Suitable for | VX base system |
| Packaging unit | 4 pc(s). |
| Net weight | 1.08 kg |
| Gross weight | 1.118 kg |
| PCF/VE (cradle-to-gate) | 5.72 |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189234 |
| Product description | VX Punched section, with mounting flange 23 x 64 mm, for inner mounting level |

Approvals

| | |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|