

**Rittal – The System.**

Faster – better – everywhere.



# VX 8619.430

## Cable clamp rail

State: 2026-01-16 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

# VX 8619.430 - Cable clamp rail Mounting angle for VX, TS, VX SE, PC & VX base/plinth system

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

## Features

Model No.	VX 8619.430
Product description	Provides strain relief for cable entries. Depth-variable mounting in a 25 mm hole pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options VX	In enclosure width 1000 mm, in the base
Installation options VX SE	In enclosure width 1000 mm, in the base
Installation options AX	In enclosure width 1000 mm, in conjunction with the AX interior installation rail and AX base configuration rail
Installation options AX stainless steel	In enclosure width + 1,000 mm
Installation options VX Base	In base/plinth width/depth 1,000 mm, in conjunction with retaining/spacer piece
Installation options VX base/plinth, stainless steel	In base/plinth width 1,000 mm, in conjunction with a M8 nut
Installation options AX Base	In base/plinth width 1,000 mm
Suitable for	AX base/plinth system VX base system VX base/plinth system, stainless steel
Dimensions	Length: 954 mm

# Features

---

Suitable for	Enclosure type: VX VX SE AX CX One-Piece Console Width: = 1,000 mm
Suitable for width	1,000 mm
Packaging unit	2 pc(s).
Net weight	5
Gross weight	5.14
Customs tariff number	73269098
EAN	4028177921955
ETIM 9	EC000322
ECLASS 8.0	27400604

---