

Rittal – The System.

Faster – better – everywhere.



AX 9206.100

Ex Enclosures

State: 2026-02-06 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



AX 9206.100 - Ex Enclosures Fiberglass Reinforced Polyester AX, empty enclosure with hinged door

Ex enclosure with hinged door, fiberglass-reinforced polyester



Features

Model No.	AX 9206.100
Version	Ex Enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EU Ambient temperature range: -40 °C...+70 °C The specified temperatures can be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection due to increased safety (Ex e), equipment protection due to enclosure (Ex tb)
Material	Housing: fiber-glass reinforced unsaturated polyester, surface resistance: < 10 \times Ω Door: glass fiber reinforced unsaturated polyester, surface resistance: < 10 \times Ω circumferentially bonded silicone gasket Mounting plate: Carbon steel, zinc-plated
Color	RAL 9011
Supply includes	Housing Door Mounting panel

Features

Dimensions	Width: 600 mm Height: 600 mm Depth: 200 mm
Dimensions of mounting plate (W x H)	505 mm x 525 mm
Material thickness – mounting plate	3 mm
Certificate IEC EX PTB 10.0011U	Yes
Certificate PTB 03 ATEX 1011U	Yes
Lock	No. of locks: 2
Protection category IP to IEC 60 529	IP 65
Protection category NEMA	Type 1 Type 3R Type 3RX Type 4 Type 4X Type 12
IK code	IK09
Operating temperature range	-40 °C...70 °C
Operating temperature	The specified temperatures can be limited by the installed equipment
Packaging unit	1 pc(s).
Net weight	17
Gross weight	17.74
Customs tariff number	94037000
EAN	4028177952102
ETIM 9	EC002503
ECLASS 8.0	27180502

Approvals

Approvals	ATEX ATEX QA IECEx IECEx QAR UR + C-UR (recognized)
Explanations	Attestation of Conformity
