Rittal – The System.

Faster – better – everywhere.





VX 8619.460 Cable clamp rail

State: 2025-10-28 (Source: rittal.com/ca-en)



VX 8619.460 - Cable clamp rail Mounting angle for VX, TS, VX SE, PC & VX base/plinth system

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

Features

Model No.	VX 8619.460
Product description	Provides strain relief for cable entries. Depth-variable mounting in a 25 mm hole pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options VX SE	In enclosure width 1800 mm, in the base
Installation options VX Base	In base/plinth width 1800 mm, in conjunction with retaining/spacer piece
Suitable for	VX base system
Dimensions	Length: 1,754 mm
Suitable for	Enclosure type: VX SE Width: = 1,800 mm
Suitable for width	1,800 mm
Packaging unit	2 pc(s).
Net weight	7.7
Gross weight	9.38
Customs tariff number	73269098
EAN	4028177921986
ETIM 9	EC000322
ECLASS 8.0	27400604

© Rittal 2025 2