### Rittal – The System.

Faster - better - everywhere.





## VX 8619.470 Bracket/Spacer

State: 2025-10-30 (Source: rittal.com/ca-en)



# VX 8619.470 - Bracket/Spacer for base/plinth system VX, carbon steel

For flexible mounting of C-profile or cable clamp rails. For installation in the VX base or on the cabinet frame profile.







#### **Features**

Model No.	VX 8619.470
Material	Die-cast zinc
Supply includes	2 retaining or spacer pieces
	Assembly components
Suitable for	Enclosure type: VX
	TS
	VX SE
Weight/packaging unit	0.298 kg
Packaging unit	2 pc(s).
Installation options	On the horizontal and vertical VX enclosure section
	On a system chassis for the inner mounting level
	On the vertical TS, VX SE enclosure section via snap-on nuts
	8800.806 or via adapter rail for VX compatibility
	On the horizontal TS enclosure section
	On the horizontal VX SE enclosure section, bottom
	On the horizontal VX SE enclosure section top, in depth
	On enclosures and rails with rectangular hole profile 12.5 x 11 mm
	On base/plinth corner piece with base/plinth trim, front and rear
	On base trim panels, lateral
For thread	M8
Suitable for	for base/plinth system VX, carbon steel
	· •

© Rittal 2025

### **Features**

Mounting tip	In VX SE on enclosure section in conjunction with adapter rail VX M8 x 16 mm cylinder screws with washers are required to fasten a C-profile rail
Net weight	0.28
Gross weight	0.289
Customs tariff number	73269098
EAN	4028177984820
ETIM 9	EC002620
ETIM 8	EC000721
ECLASS 8.0	27182003

© Rittal 2025 3