


# Rittal – The System.

Faster – better – everywhere.



## VX 8620.082

## Base/plinth trim panels, side, 200 mm, stainless steel

State: 2025-08-26 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8620.082 - Base/plinth trim panels, side, 200 mm, stainless steel For VX base/plinth systems

Stainless steel base/plinth trim panels are used depth-wise for laterally closing a base/plinth unit.

## Features

Model No.	VX 8620.082
Product description	For side completion of a base/plinth unit and for additional stabilization or the interior installation of baying bases. One 200 mm high or two 100 mm high trim panels can optionally be used to 200 mm high base/plinths.
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 400
Supply includes	Assembly components
Note	The components of the first generation base/plinth system cannot be combined with the components of the second generation base/plinth system
Dimensions	Height: 200 mm
Suitable for	Depth: = 600 mm
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
Weight/package unit	4.5 kg
Package unit	2 pc(s).
Net weight	2.94
Gross weight	3.08
Customs tariff number	94039910
EAN	4028177922426

# Features

ETIM 9	EC000721
ECLASS 8.0	27182003

# Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------