

Rittal – The System.

Faster – better – everywhere.



SV 9340.550 OM adapter

State: 2025-10-05 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.550 - OM adapter with tension spring clamp



Features

| | |
|---|--|
| Model No. | SV 9340.550 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | Chassis: RAL 7035 |
| Rated current max. | 32 A |
| Rated operating voltage | 690 V, 3~ |
| For bar systems with center-to-center spacing | 60 mm |
| Support rail type | Support frame, 1 x TS 45C, PinBlock |
| Number of poles | 3-pole |
| PinBlock | Yes |
| Dimensions | Width: 45 mm Height: 208 mm |
| Connection of round conductors | 1.5 - 6 mm ² |
| Support rails Qty/height | 1 / 10 mm |
| Suitable for busbars | Height: 5, 10 mm |
| Support frame (W x H) | 45 mm x 170 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 0.238 |

Features

| | |
|------------------------------|---------------|
| Gross weight | 0.29 |
| Copper weight (kg per piece) | 0.027 |
| Customs tariff number | 85369095 |
| EAN | 4028177502635 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV-GL Lloyds Register of Shipping |
| Explanations | Declaration of conformity Declaration of conformity UK |