

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.650 OM adapter

State: 2025-12-17 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.650 - OM adapter with tension spring clamp



## Features

Model No.	SV 9340.650
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Rated current max.	65 A
Rated operating voltage	690 V, 3~
For bar systems with center-to-center spacing	60 mm
Support rail type	Support frame, 1 x TS 55E, 1 x TS 55D-V
Number of poles	3-pole
Support frame support	Yes
Note on Model No.:	According to a heat dissipation test to IEC 61 439-1, a current carrying capacity of up to 80 A is supported
Dimensions	Width: 55 mm Height: 272 mm
Connection of round conductors	2.5 - 16 mm <sup>2</sup>
Support rails Qty/height	2 / 10 mm
Suitable for busbars	Height: 5, 10 mm
Support frame (W x H)	55 mm x 237 mm

# Features

Packaging unit	1 pc(s).
Net weight	0.339
Gross weight	0.377
Copper weight (kg per piece)	0.059
Customs tariff number	85369095
EAN	4028177502673
ETIM 9	EC001531
ECLASS 8.0	27370304

# Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK