Rittal - The System.

Faster – better – everywhere.





VX 8660.002

Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 2025-11-04 (Source: rittal.com/ca-en)

NCLOSURES

OWER DISTRIBUTION

LIMATE CONTROL

T INFRASTRUCTURI

SOFTWARE & SERVICE

VX 8660.002 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, carbon steel

Base/plinth corner pieces with trim panels for flexible cable entry.





Features

Model No.	VX 8660.002
Benefits	Reliable - very high stability of the base
	Flexible – numerous interior expansion options with the VX
	accessories
	Simple – flush finish between the baying points
Material	Base/plinth corner piece: Carbon steel
	Base/plinth trim panels, front/rear: Carbon steel
	Corner and baying covers: Plastic
Color	RAL 9005
Supply includes	4 x corner covers
	Assembly components
	4 x base/plinth corner pieces, 100 mm high
	2 x base/plinth trim panels, front/rear, 100 mm high
Note	Base/plinth trim panels, on the side for closing off a base/plinth
	unit, for additional stabilization of the bases/plinths to one another
	or for interior installation of the bases/plinths
Dimensions	Height: 100 mm

© Rittal 2025 2

Features

Suitable for	Enclosure type: VX
outable for	VX IT
	VX SE
	TX CableNet
	TS
	TS IT
	TP
	PC
	IW
	CX
	Width: = 600 mm
Type rating according to UL 50E	Type 1
	Type 12
Weight/packaging unit	4.47 kg
Packaging unit	2 pc(s).
Net weight	4.22
Gross weight	4.466
PCF/VE (cradle-to-gate)	17 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177978041
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

Approvals	UL + C-UL - FTTA
Explanations	PCF-declaration

© Rittal 2025 3