


Rittal – The System.

Faster – better – everywhere.



VX 8660.003

Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 2026-07-07 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8660.003 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, carbon steel

Base/plinth corner pieces with trim panels for flexible cable entry.



Features

| | |
|-----------------|--|
| Model No. | VX 8660.003 |
| Benefits | Reliable - very high stability of the base Flexible – numerous interior expansion options with the VX accessories Simple – flush finish between the baying points |
| Material | Base/plinth corner piece: Carbon steel Base/plinth trim panels, front/rear: Carbon steel Corner and baying covers: Plastic |
| Color | RAL 9005 |
| Supply includes | 4 x corner covers Assembly components 4 x base/plinth corner pieces, 100 mm high 2 x base/plinth trim panels, front/rear, 100 mm high |
| Note | Base/plinth trim panels, on the side for closing off a base/plinth unit, for additional stabilization of the bases/plinths to one another, or for interior installation of the bases/plinths |
| Dimensions | Height: 100 mm |

Features

| | |
|-------------------------------------|--|
| Suitable for | Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width: = 800 mm |
| Type rating according to UL 50E | Type 1 Type 12 |
| Weight/packaging unit | 5.42 kg |
| Packaging unit | 2 pc(s). |
| Net weight | 5.2 kg |
| Gross weight | 5.218 kg |
| PCF/VE (cradle-to-gate) | 19.38 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000721 |
| ETIM 8 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | VX base corner piece with base trim panel, front and rear, : 100 mm, for W H: 800 mm, carbon steel |

Approvals

| | |
|--------------|------------------|
| Approvals | UL + C-UL - FTTA |
| Explanations | PCF-declaration |
