### Rittal – The System.

Faster - better - everywhere.





# SV 9340.660 OM adapter

State: 2025-10-31 (Source: rittal.com/ca-en)



## SV 9340.660 - OM adapter with tension spring clamp



#### **Features**

Model No.	SV 9340.660
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with center-to- center spacing	60 mm
Support rail type	Support frame, 1 x TS 55D
Number of poles	3-pole
Dimensions	Width: 55 mm Height: 208 mm
Connection of round conductors	1.5 - 6 mm²
Support rails Qty/height	1 / 10 mm
Suitable for busbars	Height: 5, 10 mm
Support frame (W x H)	55 mm x 170 mm
Packaging unit	1 pc(s).
Net weight	0.29
Gross weight	0.315

© Rittal 2025

#### **Features**

Copper weight (kg per piece)	0.027
Customs tariff number	85369095
EAN	4028177502680
ETIM 9	EC001531
ECLASS 8.0	27370304

## **Approvals**

Ammanuala	ADC
Approvals	ABS
	DNV-GL
	Lloyds Register of Shipping
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3