

Rittal – The System.

Faster – better – everywhere.



TS 8800.390 Transport castors

State: 2026-03-07 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8800.390 - Transport castors for base/plinth, complete and base/plinth stationary

Locate onto the base/plinth corner piece, height 100 or 200 mm.

Features

Model No.	TS 8800.390
Product description	For locating onto the TS base/plinth corner piece 100 or 200 mm high.
Color	RAL 7022
Supply includes	4 twin castors, 2 x with, 2 x without locks.
Clearance floor	100 mm
Max. load capacity (static) per component	100 kg
Packaging unit	4 pc(s).
Net weight	9.336 kg
Gross weight	9.536 kg
Customs tariff number	83024900
ECLASS 8.0	27189262
Product description	TS Transport castor for TS base/plinth, 2 each with/without lock, static load per castor 100 kg